



PRODUCT BROCHURE · BENCHMARK SCIENTIFIC

H3770 Series NEW (Hotplate) Brochure

11 models inside · Mixing & Agitation · Hotplates & Stirrers



QUICK VIEW — SERIES AT A GLANCE

11 models in this document from Benchmark Scientific. Full specifications inside.

MODELS IN THIS DOCUMENT

H3770-H · H3770-H-E · H3770-ROD · H3770-S ·
H3770-CS · H3770-GROUP · ...

SHIP WEIGHT

6–8 lb

VOLTAGE

120 V or 230 V, 50–60 Hz (universal-input)

SOURCING

Authorized U.S. distributor

Distributed by Legacy Lab Supplies

legacylabsupplies.com · (855) 746-7557 / 855-SHOP-LLS · quotes in 24 hours



Digital Hotplates, Stirrers & Hotplate Stirrers



H3770-S



H3770-H



H3770-HS

Benchmark hotplates, stirrers and hotplate-stirrers feature an exceptionally durable, chemical resistant, white ceramic work surface. The space-efficient design (7.5 X 11.5 in. footprint) makes them ideal for use on crowded benchtops, biological safety cabinets and in bio-hoods. Advanced microprocessor controls allow quick, precise adjustment of speed and temperature. The display provides constant visualization of the speed and temperature while a safety LED indicates when the top plate is above 50°C. In addition, an optional probe is available for applications that require precise temperature control. When connected, the probe provides direct feedback to the microprocessor, which continuously adjusts and maintains the selected temperature in the sample within +/- 1°C.

With a square 7 in. work surface, all models are compatible with a wide variety of popular sizes of borosilicate glass beakers, flasks, bottles and other vessels. An optional support rod (H3770-ROD) is available for mounting thermometers, temperature probes, etc.

- Large, 7 x 7" white ceramic top plate
- Safety LED indicates hot surface
- 5L stir capacity
- Control actual temperature (with optional probe)

Technical Data

Hotplate (H3770-H)

Temperature Range:	Amb. +5 to 380°C
Platform:	7 x 7 in./ 17.8 x 17.8 cm
Control:	Digital
Dimensions: (WxDxH)	7.5 x 11.5 x 4 in. / 18 x 27.9 x 10.1 cm
Electrical Data:	115V or 230V, 50-60 Hz , 500W

Magnetic Stirrer (H3770-S)

Speed Range:	150 to 1500 rpm
Platform:	7 x 7 in./ 17.8 x 17.8 cm
Control:	Digital
Dimensions:	7.5 x 11.5 x 4 in. / 18 x 27.9 x 10.1 cm
Electrical Data:	115V or 230V, 50-60 Hz , 500W

Hotplate Stirrer (H3770-HS)

Temperature Range:	Amb. +5 to 380°C
Speed Range:	150 to 1500 rpm
Platform:	7 x 7 in./ 17.8 x 17.8 cm
Control:	Digital
Dimensions:	7.5 x 11.5 x 4 in. / 18 x 27.9 x 10.1 cm
Electrical Data:	115V or 230V, 50-60 Hz , 500W

Ordering Information

H3770-H*	Benchmark Digital Hotplate, 115V*
H3770-S*	Benchmark Digital Magnetic Stirrer, 115V*
H3770-HS*	Benchmark Digital Hotplate Magnetic Stirrer, 115V*
H3770-ROD	Optional support rod
H3770-TP	Optional temperature probe
H3770-CS	Clamp assembly with support rod and clamps for securing thermometers/probes
H3770-CSTF	Clamp Set, chemically resistant/inert teflon, includes rod and clamp

*115V with US plug. For 230v (EU plug), please add (-E).

Benchmark
Scientific



Benchmark Scientific Inc.
PO Box 709 Edison, NJ 08818
Phone: 908-769-5555
Fax: 732-313-7007
Web: www.BenchmarkScientific.com
Email: Info@BenchmarkScientific.com